5POS,AMP MCP1.5K,REC. HSG








AMP MCP 1.5K , AMP MCP Connector System

TE Part # **2137400-1**
TE Internal #: **2137400-1**
All AMP MCP, SEALED CONNECTOR HOUSING (163)

Connector Style : **Housing for female terminals**
Mating Tab Width : **1.6 mm [.063 in]**
Connector System : **Wire-to-Board, Wire-to-Device, Wire-to-Wire**
Number of Positions : **5**
Centerline (Pitch) : **4 mm [.157 in]**

ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America

Request pricing, availability and customization options

CONTACT US

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Please give us feedback:
Did you find what you need on this page?
YES NO

Feedback

DOCUMENTS | FEATURES | PRODUCT COMPLIANCE

Product Drawings

5POS,AMP MCP1.5K,REC. HSG
5POS,AMP MCP1.5K,REC. HSG English

CAD Files

Customer View Model
ENG_CVM_CVM_2137400-1_A.2d_dxf.zip
English

3D PDF
3D_CVM_CVM_2137400-1_A.pdf 3D

Customer View Model
ENG_CVM_CVM_2137400-1_A.3d_igs.zip
English

ENG_CVM_CVM_2137400-1_A.3d_stp.zip
English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style : **Housing for female terminals**
Connector System : **Wire-to-Board, Wire-to-Device, Wire-to-Wire**
Sealable : **Yes**
Hybrid Connector : **No**

Downloaded from Arrow.com.

	Primary Locking Feature : **On the Terminal** Strain Relief : **No**
Configuration Features	Number of Positions : **5** Number of Rows : **1**
Body Features	Color : **Black** Connector Code : **1** Body Material : **PBT**
Contact Features	Mating Tab Width : **1.6 mm [.063 in]**
Mechanical Attachment	Terminal Position Assurance : **Yes** Polarized : **Yes**
Housing Features	Centerline (Pitch) : **4 mm [.157 in]**
Dimensions	Width : **.61 mm [15.5 in]** Height : **1.236 mm [31.4 in]** Length : **33.5 mm [1.319 in]**
Usage Conditions	Operating Temperature Range : **-40 – 120 °C [-40 – 248 °F]**
Operation/Application	Circuit Application : **Signal**
Industry Standards	Degree of Protection : **IPX9K**
Packaging Features	Packaging Method : **Box** Packaging Quantity : **600**
Other	Connector Position Assurance Capable : **No** Serviceable : **Yes**
Statement of Compliance	Statement of Compliance pdf

Downloaded from Arrow.com.

Also in the Series | AMP MCP 1.5K



Automotive Connector Caps & Covers (1)




Automotive, Truck, Bus, & Off-Road Housings (104)

Also in the Series | AMP MCP Connector System



Automotive Connector Caps & Covers (23)



Automotive Connector Locks & Position Assurance (9)



Automotive Seals & Cavity Plugs (6)



Automotive, Truck, Bus, & Off-Road Headers (30)

Need help?

Our team is on stand-by and ready to help with your order.

CHAT NOW

© 2018 TE Connectivity. All Rights Reserved.

Downloaded from Arrow.com.