

D SUB IP 67 Top entry plastic hood 50 p

Spotted an error? |  [Print page](#)

[Back](#) 



Image is for illustration purposes only.
Please refer to product description.

- [Identification](#)
- [Version](#)
- [Technical characteristics](#)
- [Material properties](#)

Part number	09 67 050 0438
Description	D SUB IP 67 Top entry plastic hood 50 p

Identification

Category	Connector
Series of hoods/housings	D-Sub, IP67
Type of hood/housing	Shell
Description of hood/housing	With integrated cable gland
Locking type	Locking screw Thread 4-40 UNC

 [Top](#)

Version

Size	D-Sub 50
Version	Top entry
Details	Not to be used with crimp connectors.

 [Top](#)

Technical characteristics

Degree of protection acc. to IEC 60529	IP67
--	------

 [Top](#)

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black

 [Top](#)

[Login to MyHARTING](#)
for pricing and stock check

Quantity:

[Shopping cart](#) 

[Email inquiry](#) 

Need assistance?



Customer service

Your HARTING customer
service representative:

866-278-0306

customerservice-usa@harting.com

Catalogue

HARTING Device Connectivity -
Page 476



 [Browse](#)

 [Download](#)

Downloads

Title	Downloads
CAD-data 3D	 STEP
CAD-data 3D	 JT

Recently viewed - [Delete](#)



D SUB IP 67 Top entry

plastic hood 50 p

[Show product details](#)

Recently searched - [Delete](#)

Part number: [09 67 050 0438](#) (1)



HARTING contact: HARTING Inc. of N.America | Bowes Road 1370 | 60123-5538 Elgin | USA
HARTING support: 866-278-0306 | [✉ E-mail address](#) (For questions regarding products, orders and user accounts)

Website support: | [✉ E-mail address](#) (For technical problems regarding the website)



 **HARTING eChat**