



Part Number : [1727040158](#)
Product Description : FCT Knurled Thumb Screw Lock, #4-40 Thread, 43.50mm Length, Nickel-plated Brass
Series Number : 172704
Status : Active
Product Category : D-Sub Accessories
Engineering Part Number : FRS1/5

Documents and Resources

Drawings
[1727040158 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 3; 33; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:5a86502f-8977-4ad0-8526-947a742e6b76
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Accessories
Series	172704
Description	FCT Knurled Thumb Screw Lock, #4-40 Thread, 43.50mm Length, Nickel-plated Brass
IP Rating	N/A
Magnetic	Yes
Product Name	FCT Products
Type	Backshell
UPC	889056020695

Physical

Accessory Type	Locking Mechanism
Material - Body	Brass
Net Weight	3.100/g
Packaging Type	Bag
Shell Size	1, 2, 3, 4, 5
Thread Size	4-40 UNC
Thread Type	Standard

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub Connector

This document was generated on Apr 30, 2026