This document was generated on 03/14/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0010011204
Status: Obsolete
Overview: kk
Description: 5.08mm (.200") Pitch KK® Crimp Terminal Housing, 20 Circuits

Documents:
Drawing (PDF)



Series image - Reference only

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	3001
Application	Power
Overview	kk
Product Name	KK®

Physical

Circuits (maximum)	20
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm (.200")
Temperature Range - Operating	-40°C to +105°C

Material Info

Old Part Number	3001-20

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
3001Series

Mates With
3061 , 3003 , 3008

Use With
2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG, 2878

This document was generated on 03/14/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.