




Part Number : [5019390536](#)
Series Number : 501939
Status : Active - Proprietary
Product Category : Connector Housings



Drawings

[5019390536_sd.pdf](#)

Specifications


[5013300000-AS-000.pdf](#)

[SPK-501939-001-001.pdf](#)

[PS-501940-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active - Proprietary
Category	Connector Housings
Series	501939
Description	1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Single Row, Outer Positive Lock, 5 Circuits, Green
Application	Signal, Wire-to-Board
Product Name	Pico-Clasp
UPC	800756913308

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	5
Color - Resin	Green
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	61.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes

Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Pico-Clasp Vertical, Single Row, Surface Mount Headers	<u>203560</u>
Pico-Clasp Vertical, Single Row, Surface Mount Headers	<u>203561</u>
Pico-Clasp Vertical Single Row Headers	<u>501940</u>
Pico-Clasp Right-Angle, Single Row, Surface Mount Headers	<u>203562</u>
Pico-Clasp Right-Angle, Single Row, Surface Mount Headers	<u>203563</u>
Pico-Clasp Right-Angle Single Row Headers	<u>501953</u>
Pico-Clasp Vertical, Single Row, Surface Mount, Low-Halogen Headers	<u>208383</u>
Pico-Clasp Right-Angle, Single Row, Surface Mount, Low-Halogen Headers	<u>208385</u>

Use with Part(s)

Description	Part Number
Pico-Clasp Female Crimp Terminals, Gold Plated	<u>501193</u>
Pico-Clasp Female Crimp Terminals, Tin Plated	<u>501334</u>

Application Tooling

Global

Description	Part Number
-------------	-------------

Extraction Tool for Pico-Clasp Wire-to-Board Terminals, 32-28 AWG	<u>638131700</u>
---	------------------

This document was generated on Apr 26, 2026