





MATERIAL: POLYAMIDE

TOLERANCE	>0.5=3	>3=6	>6=30	>30=120	>120=400
ISO 2768-m	±0.1	±0.1	±0.2	±0.3	±0.5

RELEASE STATUS	P1	RELEASE DATE	18.08.2017	19:46:40
----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASE EC NO: 120665 DRWN: WLEUNG CHK'D: DNGUYEN62 APPR: JFMURPHY		2017/08/14 2017/08/15 2017/08/18		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
				mm		NTS									
				ANGULAR TOL ± °		DRWN BY		DATE		MX-KEL62					
				4 PLACES ±		WLEUNG		2017/08/14							
				3 PLACES ±		CHK'D BY		DATE							
				2 PLACES ± SEE CHART		DNGUYEN62		2017/08/15							
				1 PLACE ± SEE CHART		APPR BY		DATE							
				0 PLACES ±		JFMURPHY		2017/08/18		PRODUCT CUSTOMER DRAWING					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
						B				201606		2016066948			
						DOCUMENT NUMBER		DOC TYPE		DOC PART					
A		REV				2016066948		PSD		000		SHEET NUMBER			
										1 OF 1					