


37012000410 - 370 Series



Series: 370

Fuse 370 Datasheet

The 370 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to IEC 60127- 3.

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW!
Product
Selection
Guide
eCatalog
[Read Now](#)

Electronics
News and Information

SIGN UP NOW

Feedback

Electrical Characteristics		Technical Resources	Environmental Info
Property (Mouseover for details)		Value	
Ampere Rating (A)		2	
Nominal Melting I²T (A²sec)		0.98	
Interrupting Rating		35A@250VAC	
Min Operating Temp °C		-40	
Max Operating Temp (°C)		85	
Moisture Sensitivity Level		MIL-STD-202 Method 106	
Nominal Power Dissipation (W)		500	
Nominal Voltage Drop (mV)		85	
Nominal Cold Resistance (Ohms)		0.0325	
Opening		Fast-Acting (F)	
Package Size		TR5 (8.5x8mm)	
VAC (V)		250	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

- About Littelfuse
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents