

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 15440181

☐ Compare

15440181 - MTS 0.64 Female Unsealed Tin Plating Tang Terminal Assembly, Cable Range 0.60 - 0.75 mm2

☐ Compare

MTS 0.64 Female Unsealed Tin Plating Tang Terminal Assembly, Cable Range 0.60 - 0.75 mm2

Part # 15440181



[Question about this product?](#)

Attributes

Documents (2)

Part # :	15440181
Description :	MTS 0.64 Female Unsealed Tin Plating Tang Terminal Assembly, Cable Range 0.60 - 0.75 mm2
Product Type :	Terminal
Status :	✓ Active
Terminal Family :	MTS
Series :	0.64
Gender :	Female
Sealable :	Unsealed
Material :	Various (Assembly)
Weight [g] :	2
Plating :	Tin
Minimum Cable Diameter [mm] :	1.70
Maximum Cable Diameter [mm] :	1.90
Minimum Cable Core Cross Section [mm2] :	0.60
Maximum Cable Core Cross Section [mm2] :	0.75
Temperature Range :	-40 to 85

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.