











Max. Temperature: 260° during 10 seconds.


0955 269 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)
0955 269 3812 741	1	4-40 UNC		
0955 269 6811 741	2	M3		
0955 269 6812 741	2	4-40 UNC		
0955 269 7811 741	3	M3		
0955 269 7812 741	3	4-40 UNC		
Part number		PL	Nut	Index designation
		Techn. Character.		Free size tolerances
		Dat.	Name	Scale
		Detail.	25-Oct-11 Johnson.S	2 : 1
		Insp.	17-Nov-11 Steven.W	
		Stand.	17-Nov-11 Steven.W	D-Sub SMT, 15 poles Male, Straight with nuts and ground pins
EC04070		17-Nov-11	Johnson.S	
Mod.	Dat.	Name	Zhuhai HARTING Limited	TB 09 55 269 x81x
				Sub.
				Page 1/2



Detail A



Detail A



See TB 09 55 269 x81x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 269 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 269 3812 741	1	4-40 UNC		
0955 269 6811 741	2	M3		
0955 269 6812 741	2	4-40 UNC		
0955 269 7811 741	3	M3		
0955 269 7812 741	3	4-40 UNC	Index designation	
Part number	PL	Nut		

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
				Dat.	Name	Scale	D-Sub SMT, 15 poles Male, Straight with nuts and ground pins	
			Detail.	25-Oct-11	Johnson.S			
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
			Zhuhai HARTING Limited 			TB 09 55 269 x81x		Page 2/2
EC04070	17-Nov-11	Johnson.S				Sub.		
Mod.	Dat.	Name						