



Pushing Performance
Since 1945

SEK CAB FLAT COLOR TW AWG28/7 34P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 034 7006
Specification	SEK CAB FLAT COLOR TW AWG28/7 34P 30,48m
HARTING eCatalogue	https://harting.com/09180347006

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)
Description of the cable	Twisted pair

Version

Cable length	30.48 m
Number of cores	34
Core structure	AWG 28/7

Technical characteristics

Impedance	122 Ω
Limiting temperature	-20 ... +105 °C
Signal run time @ 20 °C	≤ 5.35 ns/m

Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
Material flammability class acc. to UL 94	VW-1
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 758 AVL2.E42769
----------	--------------------

Commercial data

Packaging size	1
Net weight	2,467 g
Net weight	60 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140025035
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609