Part Number : 1727040096
Product Description : FCT Metal Backshell for D-Sub Connector, Shell Size 1, Straight Cable Outlet, Large Inner Chamber, with Rubber Bushing and #4-40 Locking Screws
Series Number : 172704
Status : Active
Product Category : D-Sub Backshells
Engineering Part Number : FMK1G



Documents and Resources

Drawings

1727040096_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	172704
Description	FCT Metal Backshell for D-Sub Connector, Shell Size 1, Straight Cable Outlet, Large Inner Chamber, with Rubber Bushing and #4-40 Locking Screws
Magnetic	Yes
Product Name	FCT Products
Type	Rugged Metal
UPC	889056020077

Electrical

Shielded	Yes
Shield Type	Solid Metal

Physical

Cable Diameter	3.00-9.50mm
Material - Backshell	Zinc Die-cast
Material - Bushing	TPE
Material - Screw	Steel
Mounting Style	Locking Screw

Downloaded from Arrow.com.

Net Weight	44.000/g
Orientation	Straight
Packaging Type	Carton
Plating - Backshell	Nickel
Shell Size	1
Temperature Range - Operating	-35° to +100°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Mates With / Use With

Use with Part(s)

Description	Part Number
FCT Standard-Density D-Sub Crimp Housing, Male, Shell with Dimples, 9 Circuits, Black Front and Rear Insulator	1727040009
FCT Standard-Density D-Sub Crimp Housing, Female, Shell without Dimples, 9 Circuits, Black Front and Rear Insulator	1727040010
FCT Standard-Density D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, 500 Mating Cycles, 9 Circuits, White Insulator	1727040078
FCT Standard-Density D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, 200 Mating Cycles, 9 Circuits, White Insulator	1727040163
FCT High-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 15 Circuits	1731130058
FCT Standard-Density D-Sub Connector, Female, Straight, IDC Ribbon, 0.20µm Gold Plating, 50 Mating Cycles, 9 Circuits, Black	1727040076

Downloaded from Arrow.com.

Insulator	
FCT Standard-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 500 Mating Cycles, 9 Circuits, White Insulator	1727040075
FCT High-Density D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, 15 Circuits	1731130059
FCT High-Density D-Sub Crimp Housing, Male, 15 Circuits	1731130002
FCT High-Density D-Sub Crimp Housing, Female, 15 Circuits	1731130073
FCT Standard-Density D-Sub Connector, Male, Straight, IDC Ribbon, 0.20µm Gold Plating, 9 Circuits, Black Insulator	1727040073
FCT High-Density D-Sub Crimp Housing, Male, 15 Circuits	1731090035

Downloaded from Arrow.com.