






PART NUMBER
10138462-101LF

SL NO.	DESCRIPTION	MATERIAL	PLATING
1	SCREWABLE RECEPTACLE BODY	ALUMINIUM	PASSIVATION
2	PANEL SEALING GASKET	SILICONE	-




NOTES :-


- PART WILL BE SUPPLIED ONLY IN ASSEMBLED FORM
- SCREWS TO BE USED ARE M3 X 6MM; MATERIAL-STAINLESS STEEL
- CASTED MOUNTING PANEL SHOULD HAVE ON ITS REAR SIDE AN INTEGRAL RECTANGULAR REINFORCED RIBS OF 3MM THICKNESS AND 4MM WIDTH ALONG THE MOUNTING SCREW PLANE AT THE TOP AND BOTTOM TO ACCOMODATE THE BLIND INTERNAL SCREW THREAD

spec ref				dr	Jibin John	2016/11/08	projection 	MM 	size	A3	scale	1:1		
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Alosius, Stali	2019/01/18			ecn no	ELX-I-32499-1				
				chr	-	-			rel level			Released		
				appr	K-Paul Biju	2019/01/18	product family		OCTIS					
surface ISO 1302	linear	0.X	±0.3	Amphenol FCi	title	BULKHEAD (RECEPTACLE) - UNIVERSAL OCTIS, 26MM PITCH				dwg no	10138462		rev	D
		0.XX	±0.1											
		0.XXX	±0.05											
	angular	0°	±2°											

B



PANEL CUT OUT



	MINIMUM (mm)	MAXIMUM (mm)
A	19.7	19.9
B	31.9	32.1
C	16.5	16.8
D	M3	


PACKAGING NOTE:

1. TRAYS IN CARD BOARD BOX; 24 PCS BY TRAY

Amphenol FCI

© 2016 AFCE

D

spec ref				dr	Jibin John	2016/11/08	projection		MM		size	A3	scale	1:1
tolerance std				eng	Alosius, Stali	2019/01/18					ecn no	ELX-I-32499-1		
ISO 406 ISO 1101				chr	-	-								
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr	K-Paul Biju	2019/01/18	product family			OCTIS	rel level Released			
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCI	title	BULKHEAD (RECEPTACLE) - UNIVERSAL			dwg no	10138462		rev	D	
		0.XX	±0.1											
		0.XXX	±0.05			OCTIS, 26MM PITCH								
	angular	0°	±2°		cat. no.	-	Product - Customer Drw			sheet 2 of 2				