

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Product Highlights:

- Housing
- 2.54 mm Centerline
- Connector Type = Standard
- Number of Positions = 44
- Number of Rows = Dual

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[View Mating Products \(3\)](#)
[View Contacts \(59\)](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- [HOUSING, RCPT, DBL ROW WITH DETENTS, .100 CL. \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling
- Mating Products (3)
- Contacts (59)

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- Connector Type = Standard
- Number of Positions = 44
- Mating Type = Receptacle
- Mating Connector Lock = With
- Mating Connector Lock Type = Detent
- Mating Polarization = With
- Mounting Ears = Without
- Flame Retardant = Yes
- Color = Black
- Comment = Use Extraction Tool No. 91093-1 for round wire contacts.

Mechanical Attachment:

- Panel Attachment = Without

Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Number of Rows = Dual

Housing Related Features:

- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = FFC Cable

Other:

- Brand = AMP