Part Number : 936000046
Product Description : Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M20x1.5 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Part Number : 7000.6848.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:9a51c0d4-d874-4deb-a661-37a2c97d072d
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M20x1.5 Thread
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 4.00, 7.00, 10.00, and 13.00mm internal diameters.
IP Rating	IP66
Product Name	Heavy-Duty Connectors
UPC	887191826189

Physical

Cable Diameter	3.50-12.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	21.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	M20x1.5
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Enclosures Size A and B metal

Downloaded from Arrow.com.

	type

Downloaded from Arrow.com.