



Part Number : [2283681042](#)
Product Description : DuraClik TPA-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Tin Plating, Single Row, 150.00mm Length, 4 Circuits, Black
Series Number : 228368
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[2283681042 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	228368
Description	DuraClik TPA-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Tin Plating, Single Row, 150.00mm Length, 4 Circuits, Black
Application	Automotive, Signal, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	DuraClik TPA-to-Pigtail
Product Name	DuraClik
Type	Discrete Wire Assembly
UPC	198282852551

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Physical

Cable Length	150.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black

Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polybutylene Terephthalate (PBT), Polyamide (PA)
Net Weight	4.043/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	TPE
Wire Size mm ²	0.22

Mates With / Use With

Mates with Part(s)

Description	Part Number
DuraClik Right-Angle Single Row Headers	<u>502352</u>
DuraClik Vertical Single Row Headers	<u>560020</u>

This document was generated on Apr 30, 2026