



Connector Location A

Connector Location B




Loading-Plan

1 brown

3 blue

4 black

- Protection level: IP67
- Temperature range: -25°C ... +80°C



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
0.2	XXX=002	
0.1	XXX=001	
Step	a [m]	XXX

PVC grey, 3x0.25mm ²	21348100380XXX
Type of cable	Part no.

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
		All rights reserved		Created by STOCHECIC Stocheci		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO						Date 2018-12-17		State Final Release	
HARTING Customised Solutions				Title M8 Cable Assembly 3-poles st/- f/-				Doc-Key / ECM-Nr. 100577583/UGD/009/C 50000014.4934	
D-32339 Espelkamp		Type TB		Number 21348100380XXX				Rev. C	
								Page 1/1	