



Part Number : [1300970170](#)

Product Description : Deluxe Cord Grips Strain Relief, 3/4" NPT, Grip Body Size F3, Straight Male, Cable Diameter 15.88-19.05mm (.625-.750")

Series Number : 130097

Status : Active

Product Category : Cable Grips

Engineering Part Number : 36263



Documents and Resources

Drawings

[1300970170 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130097
Description	Deluxe Cord Grips Strain Relief, 3/4" NPT, Grip Body Size F3, Straight Male, Cable Diameter 15.88-19.05mm (.625-.750")
Hazardous Locations	Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
NEMA Rating	NEMA 4
Product Name	Deluxe Cord
Type	Strain Relief Grip
UPC	78678836263

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	0.120m (4.75")
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Aluminum
Material - Grip	Stainless Steel
Mesh Length	0.241m (9.50")

Net Weight	1.000/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

This document was generated on Apr 26, 2026