



DJI Zenmuse X4S Visual Camera

P/N:

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: 4211869

Commit: 48709

Language: en-US

Modified: 2018-03-27

Formatted: 2018-07-02

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.

Visual camera	
Model	DJI Zenmuse X4S
Technical data	https://www.dji.com/zenmuse-x4s/info#specs
Certifications	
Compliance	http://www.dji.com/euro-compliance
Documentation	
Download link	https://www.dji.com/zenmuse-x4s/info#downloads
Warranty	
Warranty	http://www.dji.com/service#warranty_period
Shipping information	
Packaging type	Cardboard box
List of contents	DJI Zenmuse X4S Visual Camera
EAN-13	7332558015070
UPC-12	845188017101

Compatible with the following products:

- 75504-0405AU; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405CN; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405EU; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405GB; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405JP; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405KR; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 75504-0405TW; FLIR M200 Therm Img Kit 336-6.8P (30Hz)
- 76404-0405AU; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405CN; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405EU; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405GB; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405JP; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405KR; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 76404-0405TW; FLIR M200 Therm Img Kit 336-6.8P (9Hz)
- 75606-0607AU; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607CN; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607EU; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607GB; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607JP; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607KR; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 75606-0607TW; FLIR M200 Therm Img Kit 640-13mm (30Hz)
- 81406-0607AU; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607CN; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607EU; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607GB; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607JP; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607KR; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 81406-0607TW; FLIR M200 Therm Img Kit 640-13mm (9Hz)
- 76007-1809AU; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809CN; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809EU; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809GB; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809JP; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809KR; FLIR M210 RTK Term Im Kit-640-19R (30Hz)
- 76007-1809TW; FLIR M210 RTK Term Im Kit-640-19R (30Hz)



DJI Zenmuse X4S Visual Camera

P/N:

© 2018, FLIR Systems, Inc.

#4211869; r. 48709; en-US

- 76607-1809AU; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809CN; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809EU; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809GB; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809JP; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809KR; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 76607-1809TW; FLIR M210 RTK Term Im Kit-640-19R (9Hz)
- 75607-1607AU; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607CN; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607EU; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607GB; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607JP; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607KR; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 75607-1607TW; FLIR M210 Therm Img Kit-640-13R (30Hz)
- 76507-1607AU; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607CN; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607EU; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607GB; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607JP; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607KR; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76507-1607TW; FLIR M210 Therm Img Kit-640-13R (9Hz)
- 76007-1708AU; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708CN; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708EU; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708GB; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708JP; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708KR; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76007-1708TW; FLIR M210 Therm Img Kit-640-19R (30Hz)
- 76607-1708AU; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708CN; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708EU; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708GB; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708JP; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708KR; FLIR M210 Therm Img Kit-640-19R (9Hz)
- 76607-1708TW; FLIR M210 Therm Img Kit-640-19R (9Hz)