



Part Number : [1301370214](#)

Product Description : Super-Safeway Factory-Wired,
3-Phase Stringer Set, 2-Sided, One Box/Phase on
3.05m Center, Color-Coded NEMA 5-20 Receptacles,
12/5 SOW Cord, L21-20 Plug

Series Number : 130137

Status : Obsolete

Product Category : Power Distribution

Engineering Number : 3095-002



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130137
Description	Super-Safeway Factory-Wired, 3-Phase Stringer Set, 2-Sided, One Box/Phase on 3.05m Center, Color-Coded NEMA 5-20 Receptacles, 12/5 SOW Cord, L21-20 Plug
Enclosure Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	3-Phase Stringer Set
UPC	78678874569

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

Physical

Cord Diameter	18.03mm (.710")
Cord Grip Body Size	F3 3/4"
Cord Length	9.14m (30.0')
Cord Type	12/5 SOW
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	12
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Sep 11, 2025

Obsolete