Part Number : 192030148
Product Description : VersaKrimp Temp-Term Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Carton
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : BB-T-325-14



Documents and Resources

Drawings

192030148_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	VersaKrimp Temp-Term Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Carton
Comments	650° F (343° C)
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800755059649

Agency

UL	E32244

Electrical

Voltage - Maximum	up to 35kV

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Nickel
Net Weight	1.001/g
Packaging Type	Carton
Stud Size	1/4" (M6)
Temperature Range - Operating	-50° to +343°C

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm^2	1.00-2.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm^2 - 0.5mm^2	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.