



**Part Number :** [1301430248](#)  
**Product Description :** Watertite Cordset 14 Gauge SOOW, 4 Pole/5 Wire, Cordset Length 7.62m (25.0'), NEMA L21-20, 208V  
**Series Number :** 130143  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 26W81A145



## Documents & Resources

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

|                    |                                                                                                 |
|--------------------|-------------------------------------------------------------------------------------------------|
| Status             | Active                                                                                          |
| Category           | Wiring Devices                                                                                  |
| Series             | 130143                                                                                          |
| Description        | Watertite Cordset 14 Gauge SOOW, 4 Pole/5 Wire, Cordset Length 7.62m (25.0'), NEMA L21-20, 208V |
| IP Rating          | IP67                                                                                            |
| NEMA Configuration | NEMA L21-20                                                                                     |
| Product Name       | Watertite                                                                                       |
| Specialty          | N/A                                                                                             |
| Type               | Cordset                                                                                         |
| UPC                | 78678863042                                                                                     |

### Agency

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E38085 |

### Electrical

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 20.0A   |
| GFCI                          | No      |
| Voltage - Maximum             | 3Ø 208V |

### Physical

|                     |               |
|---------------------|---------------|
| Cord Grip Body Size | F3 3/4"       |
| Cord Type           | 12/3 SOOW     |
| Flange              | No            |
| Flip Lid            | No            |
| Gender              | Male-Female   |
| Length              | 7.62m (25.0') |
| Lighted Connector   | No            |
| Locking Blade       | Yes           |
| Net Weight          | 288.000/kg    |
| Poles               | 4-pole/5-wire |

|                 |        |
|-----------------|--------|
| Receptacle Type | Single |
|-----------------|--------|

This document was generated on Sep 05, 2025