

## 2-Port USB to DB9 Serial FTDI Adapter Cable with COM Retention (M/M), 6 ft. (1.83 m)

MODEL NUMBER: U209-006-2



Connect 2 devices with 9-pin RS-232 serial ports to the USB-A port on your computer, laptop or tablet. Recommended for connecting modems, digital cameras, PDAs and ISDN terminals.

### Features

#### Connects 2 DB9 Devices to a USB-A Device

- Recommended for connecting a modem, digital camera, PDA or ISDN terminal to your computer, laptop or tablet
- Supports data transfer speeds up to 225 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 6 ft. design fits perfectly into laptop bag
- COM retention for automatic reassigning of COM values to ports in case of disconnection or reboot
- Integrated FTDI FT232RL chipset

#### First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket easy to install in tight spaces

#### Broad Compatibility

- Compatible with Windows, Mac and Linux operating systems

## Specifications

OVERVIEW	
UPC Code	037332198303

### Highlights

- Supports data transfer speeds up to 225 Kbps
- Premium foil and braid shielding reduces EMI/RFI line noise
- Compatible with Windows®, Mac® and Linux® devices
- No external power source required
- Integrated FTDI FT232RL chipset

### System Requirements

- Computer or other device with available USB port and Windows XP or later, Mac OS X 10.3 and later, or Linux operating system

### Package Includes

- U209-006-2 2-Port USB to DB9 Serial FTDI Adapter Cable (M/M), 6 ft.
- Driver CD
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.50
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) DB9 (MALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	2.00 x 4.90 x 5.00
Shipping Dimensions (hwd / cm)	5.08 x 12.45 x 12.70
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Packaging Type	Box
Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.