

	1	2	3	4	5	6	7	
A	Material Item 1 : Terminal housing:Thermoplastic (UL94V-0),Green Item 2 : Clamp: Brass , Ni plated Item 3 : Wire guard solder pin: Brass ,Tin plated Item 4 : Terminal screw: Steel Zinc plating “-” slot type Electrical cULus Voltage rating: 300V Current rating: 20A Wire range: Solid wire(AWG): 12-22 Stranded wire(AWG): 12-22 Torque(Lb-In): 3.5 Screw: M3 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:							A
B								B
C								C
D								D
E								E
F								F
G	RECOMMENDER PCB LAYOUT							G
H	Customer-No. ASSMANN WSW-No. A-TB508-TUxx Drawing-No. ASS 0652 CO rev02 Replace Sheet							H