
HellermannTyton

Technical data sheet

Article number:
111-02811 T18S



Product Group	Cable ties polyamide 6.6 standard
Product Family	T-Series in PA66 black
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Diameter max (metric)	16.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	3.2 mm
Length (L)	83.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	1000 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL | csa-C22.2 no. 62275, UL | ANSI/UL 62275
Thickness (T)	0.95 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E85319
Variant	Inside Serrated
Width (W)	2.3 mm

HF RoHS

c UL us

created on 6. September 2024, 5:02 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.