



Part Number : [1727040004](#)
Product Description : FCT Standard-Density D-Sub Crimp Housing, Female, Shell without Dimples, 25 Circuits, Black Front and Rear Insulator
Series Number : 172704
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : FL25S7-K121



Documents and Resources

Drawings
[1727040004 sd.pdf](#)

3D Models and Design Files
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	172704
Description	FCT Standard-Density D-Sub Crimp Housing, Female, Shell without Dimples, 25 Circuits, Black Front and Rear Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Standard Density
UPC	889056019057

Electrical

Shielded	Yes
----------	-----

Physical

Circuits (Loaded)	0
Circuits (maximum)	25
Color - Resin	Black
Gender	Female
Material - Resin	Polybutylene Terephthalate (PBT), Polyamide (PA)
Material - Shell	Steel
Net Weight	9.500/g

Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shell Size	3
Temperature Range - Operating	-55° to +115°C
Termination Style	Crimp
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size (AWG)	18, 20, 22, 24, 26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Standard-Density D-Sub, Size 3, 25 Position, Plug

Use with Part(s)

Description	Part Number
FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 24-20 AWG, 500 Pieces	<u>1731120214</u>
FCT Machined Contact, Female, Crimp, 0.80µm Gold Plating, Split Tine, 24-20 AWG, 500 Pieces	<u>1731120215</u>
FCT Machined Contact, Female, Crimp, 1.30µm Gold Plating, Split	<u>1731120216</u>

Tine, 24-20 AWG, 500 Pieces	
-----------------------------	--

This document was generated on Apr 30, 2026