

Waterproof pH/mV/Temperature Kit

3-in-1 Meter with Lab-Quality Performance
Measures pH, mV, and Temperature at your workbench or in the field

Features:

- Waterproof housing (meets IP57)
- Automatic calibration (4, 7, and 10pH)
- Choice of 3 point calibration for better accuracy
- Automatic Temperature Compensation
- Memory stores up to 200 readings with series number, measured value and temperature
- Large blue backlit dual LCD display
- Auto power off saves battery life with disable function
- Complete with pH/mV/Temperature electrode, protective rubber holster, pH calibration solutions (4, 7, and 10pH), 2 AA batteries, and hard carrying case



Specifications	
pH	-2.00 to 19.99pH
mV	-1999 to + 1999mV
Temperature	32 to 212°F (0 to 100°C)
Resolution	0.01pH, 1mV, 0.1°
Accuracy	±0.02pH; ±0.15mV; ±1°F/±0.5°C
Power	Two AA batteries
Dimension	Meter: 4.7 x 2.6 x 1.2" (120 x 65 x 31mm) Kit: 14 x 10.75 x 3" (355.6 x 273 x 76.2mm)
Weight	Meter: 6.3oz (180g) Kit: 2.9lbs (1.3kg)

Ordering Information:

PH300Waterproof pH/mV/Temperature Kit
PH305Spare pH/mV/Temperature Electrode

