


CATALOG LISTING
BM-2R559729-A4
 PAGE 1 OF 1
M
 ISSUE 2
 REVISIONS
 A 0035413
 JA 07DEC07
 J A S 30 JUN 98 CHECK J A F 1 JUL 98 CHECK ASD 07DEC07
 RASTER
 DRAWN
 J A S 30 JUN 98 CHECK J A F 1 JUL 98 CHECK ASD 07DEC07
 RELEASE NO. PR-23556
 REPLACES
 X110440-BM



NOTE
 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF Ø.139 MAX ON 1.000 ± .002 CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL						
OPERATING FORCE ----- 15 - 25 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT						
RELEASE FORCE ----- 8 OZ MIN	22A 125, 250 OR 277 VAC 3/4 HP 125 VAC, 1 1/2 HP 250 VAC L167	TOLERANCES APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±						
DIFFERENTIAL TRAVEL ----- .003 MAX	L288 L315 L318	<table border="1"> <tr> <th>DES. UNITS</th><th>SI METRIC</th><th>US CUSTOMARY</th></tr> <tr> <td></td><td>☐</td><td>☒</td></tr> </table>	DES. UNITS	SI METRIC	US CUSTOMARY		☐	☒
DES. UNITS	SI METRIC	US CUSTOMARY						
	☐	☒						
OVERTRAVEL ----- .005 MIN	22A 250V ~ T85 5E4	WEIGHT .050 LB						