
PX0857/2M00 Datasheet

Product Name // Overmould Flex Connector PX0857 Series
Pre-Wired Patch Cord IP68 RJ45 to Shielded RJ45 2M Cable

View Product Page





// Product Description:

- Cat 8 specification (25Gbps)
- Pre-Wired Patch Cord with overmoulded connector on one end
- Water and dustproof to IP68 when mated with compatible connector
- Fully shielded system
- S-FTP cable construction
- PVC jacket cable
- IP68 RJ45 to RJ45
- Supplied with PX0835 Sealing Cap to maintain IP rating of unmated connectors
- Mate with all PX08 Standard Series RJ45 Panel Mount Connectors

// General Information:

Product Display Title:	Cat 5e, Cat 6a & Cat 8 Options
Product Family:	Circular Data Connectors
Product Series:	Standard Buccaneer - Ethernet
Body Colour:	Black
Body Material:	PA
Body Material Type:	Plastic Body
Cable Length:	2m
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	1.5A
Data Cable Type:	IP68 RJ45 to Shielded RJ45
Diameter Over Coupling Ring Mm:	38.1mm
Durability:	1200 cycles
Ethernet Category:	Cat 8
Flamability Rating:	UL94V-2
Ip Rating:	IP68, IP69K
Max Operating Temperature:	+60°C
Min Operating Temperature:	-20°C
Number Of Contacts:	8 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
Sheath Colour:	Black
Sheath Material:	PVC
Voltage Max:	72V

// Product PDF Links

Standard Series Ethernet...

// Product 3D CAD Model Links

PX0857/2M003D CAD Model

Have a question or project enquiry you'd like to talk to us about?

Click Here To Contact Us

Downloaded from Arrow.com.