

Cable Sealing f. Split Hood OD 13.5~15mm



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Type of accessory	Cable seal
Description of the accessory	Han® Split Hood 1 cable entry Wide version

Technical characteristics

Clamping range	13.5 ... 15 mm
----------------	----------------

Material properties

Material (accessories)	NBR
Colour (accessories)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	8 g
Country of origin	China
European customs tariff number	84849000

Page 1 / 2 | Creation date 2025-10-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Hartung-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Commercial data

GTIN	5713140191761
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431