

[Find by Feature](#)
[Browse by Category](#)
[Share](#)
 [Search →](#)

Enter part number or keyword

[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Terminal ▼

Results with your selections: --

Blade size [mm] ▼

Terminal family ▼

Material ▼

Plating ▼

Gender ▼

Sealed ▼

Inside Ring Diameter [mm] ▼

Outside Ring Diameter [mm] ▼

Minimum Cable Core Cross Section [mm²] ▼

Maximum Cable Core Cross Section [mm²] ▼

Minimum Cable Diameter [mm] ▼

Maximum Cable Diameter [mm] ▼

[Clear](#)
[Search →](#)

Female Metri-Pack 630 Special Tin Plated Terminal, Cable Range 0.80 - 0.50 mm², Cable Insulation Range 3.12 - 2.03 mm

Part #12015864

[Question about this product?](#)

[Attributes](#)
[Documents \(4\)](#)

Part #:	12015864
Description:	Female Metri-Pack 630 Special Tin Plated Terminal, Cable Range 0.80 - 0.50 mm ² , Cable Insulation Range 3.12 - 2.03 mm
Product Type:	Terminal
Status:	Active
Blade size [mm]:	6.3
Terminal family:	Metri-Pack
Series:	630 SPL
Gender:	Female
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin
Minimum Cable Core Cross Section [mm²]:	0.50
Maximum Cable Core Cross Section [mm²]:	0.80
Minimum Cable Diameter [mm]:	2.03
Maximum Cable Diameter [mm]:	3.12

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.