Part Number : 2451360410
Product Description : Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 1.0m Length, Gold (Au) Plated, 4 Circuits, Black
Series Number : 245136
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2451360410_sd.pdf

2027040010-PK.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	245136
Description	Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 1.0m Length, Gold (Au) Plated, 4 Circuits, Black
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mega-Fit-to-Mega-Fit
Product Name	Mega-Fit
Type	Overmolded Assembly
UPC	889056878180

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V AC

Physical

Cable Length	1.0m
Circuits (Loaded)	4
Circuits (maximum)	4

Downloaded from Arrow.com.

Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	204.800/g
Number of Rows	2
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	5.70mm
Plating min - Mating	0.381µm
Plating min - Termination	0.381µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Size (AWG)	12

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mega-Fit Right-Angle, Dual Row, Through Hole Headers	172064
Mega-Fit Vertical, Dual Row Through Hole Headers	172065

Downloaded from Arrow.com.