Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
- FLOS & FLOS+
- Power
  - Accessory
  - PWC
  - PWCU
  - PWE
  - PWF
  - PWG
  - PWH
  - PWL
  - PWM
  - PWMU
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





PWH-03PMMB-SC7001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +



Power, PWH,...
PWH-03AFFM-...
-20°C ~ +80°C
− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **25A**	Connector Type **Receptacle**
Shielded **Plastic, Non-shielded**	No. of Contacts **03**
Connector Gender **Male**	Backshell **Circular**
Mating Style **Screw Thread**	IP Rating **IP67**
Assembly Style **Screw-in**	

More Options

People Also Bought



PWH-03PMMB-...



1DC-05BFFM-LL6A02



BD-05BMMA-QL8SN0



BA-04AFFM-SL7A03



BB-04BFFA-QL8MPP

Downloaded from Arrow.com.