



Powering Business Worldwide

pe.eaton.com

Single Row Terminal Block

LP207102MPR53

UPC:051712393560

Dimensions:

- **Height:** .001 IN
- **Length:** 1.93 IN
- **Width:** .65 IN

Weight: .1 LB

Warranties:

- Not Applicable

Specifications:

- **Application:** industrial
- **Mounting:** Flat base, barrier end
- **Special Features:** Break down voltage 3400V, flat base/barrier end
- **Type:** Barrier
- **Voltage Rating:** 150V
- **Number Of Poles:** Two-pole
- **Operating Temperature:** -40° to 105°C
- **Options:** Mounting plates
- **Wire Size:** #22-12 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.375 in
- **Screw Options:** Standard screw
- **Material:** Molded thermoplastic, zinc plated philslot screw
- **Color:** Black
- **Connection:** #6-32 TPI screw
- **Terminal Material:** Extended pin

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked



- RoHS Compliant

© 2016 Eaton. All rights reserved.