

Product data sheet

Specifications



APC IT Power Distribution Module 2 Pole 3 Wire 30A L3-L1 L6-30 380CM

PDM2330L6-31-380

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
--------------	--

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.4 cm
Depth	40.6 cm
Net weight	4.29 kg

Input

Network frequency	60 Hz
Max line current	30 A

Output

Max current draw	30 A
Number of power socket outlets	1 NEMA L6-30R

Conformance

Product certifications	UL listed
------------------------	-----------

Environmental

Ambient air temperature for operation	0...30 °C
Relative humidity	0...95 %

Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...4572.00 m

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	40.6 cm
Package 1 Length	44.4 cm
Package 1 Weight	5.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)