






REV.	DATE	DESCRIPTION
A	01/23/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED
MOUNTING HOLES

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						01/23/04
6	FERRULE	COPPER	GOLD	1		CHECKED			PART DESCRIPTION SMA BULKHEAD CRIMP JACK (FOR RG-58C/U, 58/U CABLE)				
5	LOCK WASHER	BRASS	GOLD	1		ISSUED							
4	HEX NUT	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 132118				
3	CONTACT PIN	BER. COPPER	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 132118.DWG REV. A SIZE A SCALE NA				
1	BODY	BRASS	GOLD	1									
DESCRIPTION						CAD FILE							
					DO NOT SCALE DRAWING	C:/132/132118.DWG							