





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/28/04	



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL-94V-0

Insulator color: Black

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 1 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions / 2 + .300 [7.60]

B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]

C = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	7/28/04
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE
 BOX HEADER, RIGHT ANGLE PCB MOUNT,
 2 ROW .100 PITCH, GOLD FLASH PLATED

SIZE X	PART NO. BHR-XX-HUA	REV. -
REF:	SCALE: NTS	SHEET 1 OF 1