





Connector Location A

Connector Location B





X
male
(without protection cap)

Y
male
(without dust cap)



Loading Plan



- Temperature range: -40°C ... +85°C

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by 402676 Gross	Inspected by 402676 Gross	Standardisation COSTEA Costea	Date 2022-08-31	State Final Release	
	Department HCS - RO	Title FO CA PP2-LCdx, 50µ, OM3, PUR				Doc-Key / ECM-Nr. 100677880/UGD/009/F 500000219506	
	HARTING Customised Solutions D-32339 Espelkamp	Type TB	Number 3361431XXX0002			Rev. F	Page 1/2

	1	2	3	4	5	6	7	8
A								
B								
C	27	33614311000002	FO Breakout Cable, MM, 50/125µm, PUR, black, bend tolerant OM3	100	±1%			
	26	33614310900002		90				
	25	33614310800002		80				
	24	33614310700002		70				
	23	33614310600002		60				
	22	33614310500002		50				
	21	33614310450002		45				
	20	33614310400002		40				
	19	33614310350002		35				
D	18	33614310300002		30				
	17	33614310250002		25				
	16	33614310200002		20				
	15	33614310150002		15				
	14	33614310140002		14				
	13	33614310130002		13				
	12	33614310120002		12				
E	11	33614310110002		11				
	10	33614310100002		10				
	9	33614310090002		9				
	8	33614310080002		8				
	7	33614310070002		7				
	6	33614310060002		6				
	5	33614310050002		5				
	4	33614310040002		4				
F	3	33614310030002		3	±0.03			
	2	33614310020002		2				
	1	33614310010002		1				
	Cont. no.	Part no.	Type of cable	Dim. a[m]				



All rights reserved

Department HCS - RO

Created by
402676
Gross

Inspected by
402676
Gross

Standardisation
COSTEA
Costea

Date
2022-08-31

State
Final Release

Doc-Key / ECM-Nr.
100677880/UGD/009/F
500000219506

HARTING Customised Solutions
D-32339 Espelkamp

Type
TB

Number
3361431XXX0002

Rev.
F

Page
2/2

All Dimensions
in mm

Tech. Character.

Free size tol.

According to production drawing