

**CB 98/2,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

|            |                                             |
|------------|---------------------------------------------|
| Version    | Cable ties, 2.5 x 98 mm, Polyamide 66, 80 N |
| Order No.  | <a href="#">1278600000</a>                  |
| Type       | CB 98/2,5 NC                                |
| GTIN (EAN) | 4008190154554                               |
| Qty.       | 100 pc(s).                                  |

Creation date October 1, 2024 1:05:50 PM CEST

Catalogue status 28.09.2024 / We reserve the right to make technical changes.

## CB 98/2,5 NC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 1.1 mm | Depth (inches)  | 0.043 inch |
| Height     | 98 mm  | Height (inches) | 3.858 inch |
| Width      | 2.5 mm | Width (inches)  | 0.098 inch |
| Net weight | 0.24 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...85 °C |
|-----------------------------|-------------|

## Installation materials

|                                   |       |                                   |              |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max.             | 21 mm | Bundle diameter, min.             | 1 mm         |
| Cable diameter, max.              | 21 mm | For re-opening                    | No           |
| Halogen                           | No    | Material                          | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 80 N  | Tensile strength (Pound-force)    | 18 lbf       |
| UL 94 flammability rating         | V-2   | UV-resistant                      | No           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0    | EC000046    |
| ETIM 8.0    | EC000046    | ETIM 9.0    | EC000046    |
| ECLASS 9.0  | 27-14-07-02 | ECLASS 9.1  | 27-14-07-02 |
| ECLASS 10.0 | 27-14-07-02 | ECLASS 11.0 | 27-14-07-02 |
| ECLASS 12.0 | 27-14-07-02 | ECLASS 13.0 | 27-14-07-02 |
| ECLASS 14.0 | 27-14-07-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## Approvals

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E317499    |

## Downloads

|                                             |                                          |
|---------------------------------------------|------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">DE PI830000 160627 001</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a> |

### CB 98/2,5 NC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

