



Roll over image to zoom in

RapidRun® HDMI® Single Gang Wall Plate Transmitter with VGA, Stereo Audio and USB - Aluminum

Use with a RapidRun Optical Runner and Receiver Flying Lead for a complete, high-performance HDMI audio/video solution

★★★★★

0 Reviews

Product # : 60140

Connector 1 : (1) HDMI Female, (1) VGA Female, (1) USB-B Female, (1) 3.5mm Stereo Female

Connector 2 : (1) RapidRun Optical Female, (1) VGA Female, (1) 3.5mm Stereo Female, (1) USB-A Female

11 In Stock & ready to ship!




Add



Need it shipped today?

Place your order before the timer runs out!



print share chat

Product Info

★ Customer Reviews

? Questions & Answers

🌐 Distributors

... More Choices

Description

Features

Specs

Support

Product Description

RapidRun Optical is designed to be the standard for in-wall HDMI audio/video installations. Using pre-terminated break-away flying leads and wall plates with an in-wall runner ensures flexible, efficient, high quality connections for all types of equipment, with no field terminations. Ideal for high resolution displays utilizing HDMI, this wall plate transmits HDMI signals through an Optical runner cable and features VGA, 3.5mm Stereo Audio, and USB pass through ports to allow for a clean termination.

Please note:

- Some HDMI source devices are unable to output the power required to send A/V signals over the Optical runner cable which results in no image being displayed. In those instances, an HDMI Voltage Inserter ([42223](#) or [42236](#)) may be required.

Each complete RapidRun Optical solution requires a break-away flying lead or wall plate to terminate each end of the runner cable. Each runner requires (2) break-away flying leads OR (1) wall plate and (1) break-away flying lead.

- Download a PDF with the technical specifications of this product on the Support tab or view the technical specifications of this product on the Specs tab
- Download a PDF of the Quick Start Guide for this product on the Support tab

Product Features

- Supports full 1080p, 4k, and 3D HDMI features
- Utilizes fiber cabling, so it is resistant to EMI/RFI interference
- Powered with USB at the display side (RX)

 **WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Specifications

Color :	Aluminum
UPC :	757120601401
Warranty :	3 Years
Vendor :	C2G
Weight :	0.342 LB

- Download a PDF with the technical specifications of this product on the Support tab
- Download a PDF of the Quick Start Guide for this product on the Support tab

Electrical Specifications

- Resolutions Supported: 4k x 2k 60Hz, 4k x 2k 30Hz, 1080p, 720p, 480p
- HDMI Features Supported: Ethernet Return Channel, HDMI High Speed, HDCP, EDID, CEC,
- Audio Return Channel
- Power Consumption: Max 5V @ 135mA
- Idle: 5V @ 125mA
- Normal Operation: 5V @ 128mA

Physical Characteristics

- Pigtail Length: 4 inches
- Color Designation: Platinum
- Temperature Rating: 0°C ~ 70°C
- Humidity: 0% ~ 90% RH
- Bend Radius: 5mm
- Compliance: CE, FCC, RoHS2

Product Support

Downloads

- Download the [quick start guide](#)
- Download the [technical specifications](#)

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)

