



PART FINDER

FIND NOW

Find faster what you're looking for!

Product Overview

Connectors

Thermal management

Cable assembly

Customer specific solutions

Power cords

D SUB cable assembly

Modular cable assembly

USB cable assembly

USB Type C

Audio- & video cables

SATA cable

Flat ribbon cable

FFC cable

Fiber Optic Cables

Capabilities

IT Network Products



download
technical drawing

Flat ribbon cable

AK AWG10

Flat Ribbon Cable

Flat cable, pitch 1.27mm, 10 poles, grey, UL2651, reel 30.5, AWG28

Part number: AK AWG10

product group: Flat Ribbon Cable

style: Flat cable

pin count: 10

pitch in mm: 1.27

current rating: 1A

version: grey, UL2651

packaging: reel 30.5

AWG: AWG28

insulator: PVC

USB 3.1 Cable Assemblies with PD-funktion

Download the Newsletters



MORE NEWS



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, A
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)



[PART FINDER](#)

[IMPRINT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[PRIVACY POLICY](#)

[PRINT](#)

[RECOMMEND](#)