



**Part Number :** [1301460065](#)

**Product Description :** Watertite Extreme Connector for Male Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, F2, Silicone Husk

**Series Number :** 130146

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 15W47MB




---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Connector for Male Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678875358

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No

Net Weight	146.190/g
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Dec 31, 2025