

Representative Image

Catalog No. TC140

Description: SADDLE SPRT MTG BASE .5X.4IN NAT NY

UPC No 5414363058199

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 14.29mm (0.563 Inches), Width of 8.73mm (0.344 Inches), Height of 6.75mm (0.266 Inches), Mount with #4 Screw, Bulk Pack

Descriptors

Category	Cable tie mounts
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Application	Used for wire bundles, cables, and hoses to panels

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#4

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	14.29 mm
Length	0.56 inch
Width	8.73 mm
Width	0.34 inch

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Height	6.75 mm
Height	0.27 inch
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.