





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/17/20	
A		UPDATE DRAWING	2/26/20	AY/KL
B		UPDATE DIM.	4/24/20	AY/NL



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-2
 Contacts: Brass
 Plating:
 Tin over Copper underplate overall
 Electrical:
 Current rating: 7.0 A
 Voltage rating: 250V AC, DC
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 1,500 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		TITLE .200 [5.08] POWER HEADER, STRAIGHT WITH LOCK POLARIZER, 4P, REMOVED PIN 2	
DRAWN	AY	1/17/20			
CHECKED	KL	1/17/20			
APPROVED					
SIZE X		PART NO. LHF-04-SA1-X02-V2		REV B	
REF: S00123T		SCALE: NTS		SHEET 1 OF 1	