







LOC		DIST		REVISIONS					
HV		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	ECO-09-020745	23SEP2009	DS	AT



SCALE 2:1



SECTION G-G

- 1 MATERIAL:
TYPE: PA66 35%GF
COLOR: SEE TABLE
- 2 SEALING SURFACE, NO WITNESS LINE,
DAMAGE, OR FLASH PERMITTED
3. FEATURES DENOTED BY REFERENCE DIMENSIONS
MUST BE INSPECTED FOR PRESENCE
- 4 PRELIMINARY PART—NOT RELEASED FOR PRODUCTION

1587722-1 SHOWN

4	13.40	ORANGE	9.90 - 10.50	1587722-2
	12.25	BLACK	8.10 - 9.30	1587722-1
	E	COLOR	CABLE DIA	PART NO

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION, ALL RIGHTS ARE RESERVED.		DWN D. SIMPSON 12JAN2009	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK A. TYLER APVD	NAME CABLE SEAL RETAINER HVA280-3PM CHART	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.15 2 PLC ±0.10 5 PLC ±0.05 4 PLC ±.1 ANGLES ±1° FINISH -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	SIZE A100779C=1587722 SCALE 1:1 SHEET 1 OF 1 REV A	