



APPROVED: _____
 DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	8/28/14	
A		UPDATE SPEC.	8/7/20	AY/EY



RECOMMENDED PCB LAYOUT



SECTION A-A



SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: Green
 Contacts: Copper Alloy, Tin plated
 Electrical:
 Voltage rated: 300 V
 Current rated: 15 A
 Withstanding voltage: 1600V AC/1 Min
Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



Positions: 02 thru 24
 A = .200 [5.08] x No. of Positions+ .055 [1.40]
 B = .200 [5.08] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010		TITLE				
APPROVALS		DATE				
DRAWN AY 8/28/14		.200 [5.08] PITCH, EURO BLOCK HEADER RIGHT ANGLE, CLOSE SIDE				
CHECKED YC 8/28/14		SIZE X		PART NO. EBQA-XX-D-C		REV. A
APPROVED		REF: S00067C		SCALE: NTS		SHEET 1 OF 1