



Part Number : 1301050050

Product Description : LOVOLT 400W 120V/12V Workstation with 4 Receptacles 15A Breaker, 16/3 SOOW Cord Type, 1.83m (6.0') Cord Length

Series Number : 130105

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1640-12



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130105
Description	LOVOLT 400W 120V/12V Workstation with 4 Receptacles 15A Breaker, 16/3 SOOW Cord Type, 1.83m (6.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 3R
Product Family	Specialty Lighting
Product Name	Woodhead
Type	Hand Lamps, Specialty Light
UPC	78678862520

Electrical

Lamp Wattage - Maximum	400W
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	N/A
Cord Length - Primary	1.83m (6.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	80.01mm (3.150")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	206.25mm (8.120")
Lamp Type	N/A
Length	285.75mm (11.250")
Material - Guard	N/A
Outlet	2 - 60W07 Non-NEMA Crow Foot
Packaging Type	Carton

This document was generated on Sep 26, 2024