

Specifications

Eaton KU8



Eaton Bussmann KU series panel mount terminal block connector, 600 V, 60 A, Double row, Standard, 8-pole, 10-32 TPI Screw, Black, Nickel-plated brass terminal



General specifications

PRODUCT NAME	Eaton Bussmann KU series panel mount terminal block connector
CATALOG NUMBER	KU8
UPC	051712847070
PRODUCT LENGTH/DEPTH	6.25 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	Contact Manufacturer

Electrical ratings

AMPERAGE RATING	60A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Eight-pole
TYPE	Double row, standard

Resources

CATALOGS [Bussmann series complete full line catalog no. 1007](#)

[KU8~TERM BLOCK BLACK NOR](#)

MULTIMEDIA [Bussmann series Fuseology](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

