

[Home](#)
[Products](#)
[Promotions](#)
[News](#)
[Grow your Business](#)
[Contact](#)
[Order Now](#)


Find Honeywell product info in one mouse click:

Datasheets, virtual tour, images, partnumbers, ...

Product Quickfinder


[Home](#) > [Products](#) > [Industrial Scanners](#) > [Granit 198Xi](#)

Granit 198Xi



Download

Select a datasheet



The Granit 1980i (Corded) and 1981i (Cordless) industrial scanner features full-range area-imaging technology capable of reading both 1D and 2D barcodes from six inches (15 cm) to over 50 feet (15 meters). From poor quality 7.5 mil paper codes scanned at arm's length to 100 mil retro-reflective codes hanging from warehouse rafters, the 198Xi is built to read virtually all barcodes across its unmatched range, supporting maximum operator productivity in the harshest environments.

Specifications

Industrial Grade Cable Option: Tested to withstand 300,000 90-degree bends at temperatures as low as -22°F (-30°C). Continues to communicate when up to 60 pounds of force is applied.

Single Scanning Solution: Can replace and consolidate multiple purpose-built scanners in typical distribution centre and warehouse environments.

Full-Range Area-Imaging Performance: Scan virtually all 1D and 2D barcodes from 6 in (15 cm) to over 50 ft (15 m) away.

Built Granit Tough: Tested to withstand the toughest environments, Granit is rated IP65 and can withstand 5,000 tumbles from 3.2 ft (1 m) and 50 drops to concrete from 6.5 ft (2 m).

Easy to Use: A laser-spot aimer, omnidirectional scanning, and features such as centre-decode take the guesswork out of scanning at extended ranges.

Granit 1980i Industrial Scanner

Granit 1980i Industrial Scanner - Corded

1980iFR-3SER SER Kit: 1D/2D, FR focus, red scanner (1980iFR-3) and RS232 Industrial Grade cable (CBL-020-300-C00-01). Regional Power Supply needs to be ordered separately. 664,89 385,64

1980iFR-3USB USB Kit: 1D/2D, FR focus, red scanner (1980iFR-3), USB, black, Type A, 3m (9.8), straight, 5v host power, industrial grade (CBL-500-300-S00-03), with vibrator 664,89 385,64

1980iFR-3 Scanner, 1D/2D, FR focus, red, RS232/USB, with vibrator 633,81 367,61

Granit 1981i Industrial Scanner - Cordless

1981iFR-3SER-5 SER Kit: 1D/2D, FR focus, red scanner, Bluetooth Class 1 (1981iFR-3), charge & communication base (CCB05-100BT-07N), RS232 Industrial Grade cable (CBL-020-300-C00-01). Regional Power Supply needs to be ordered separately. 1014,54 588,43

1981iFR-3USB-5 USB Kit: 1D/2D, FR focus, red scanner, Bluetooth Class 1 (1981iFR-3), charge & communication base (CCB05-100BT-07N), USB, black, Type A, 3m (9.8), straight, 5v host power, industrial grade (CBL-500-300-S00-01), with vibrator 1014,54 588,43

1981iFR-3 Scanner, 1D/2D, FR focus, red, Bluetooth Class 1, with vibrator 729,27 422,98

Stands/Holders/Cordless Bases/Access Points	+
Cables	+
Chargers & Power	+
Heater	+
Service & Repair - Scanner Service Contracts	+

Sitemap

[Home](#) [Products](#) [Promotions](#) [News](#) [Grow your Business](#) [Contact](#) [Order Now](#)

[Scansource Europe](#) | [Honeywell](#) | [Terms of Use](#) | [Webdesign by Blue4You](#)

Cookie Control

This site uses cookies to store information on your computer.

[read more](#)

Contact

Call your local freephone number to get in touch with a ScanSource Europe Account Manager. Click the button below to find the overview of the available ScanSource Europe freephone numbers.

[▶ Freephone numbers](#)

© Copyright 2012 ScanSource Honeywell