




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A2	CHANGE TO BE NON-BOOT/ NON-MOLDING		18/01/07	
A3	CHANGE SR FROM BOOT TO MOLDING		01/03/2007	
A4	CHANGE INSULATION FROM Ø1.0mm TO Ø1.1mm & US PLUG		26.11.2014	
A5	ADD COLOR BLACK.		23/May/2015	
A5	ADD LENGTH 6".			



LENGTH & P/N Table

LENGTH	P/N
6 inch±0.8 inch	MP-54RJ45SNNX-006in
2FT±1.2 inch	MP-54RJ45SNNX-002
3FT±1.2 inch	MP-54RJ45SNNX-003
5FT±2 inch	MP-54RJ45SNNX-005
7FT±2 inch	MP-54RJ45SNNX-007
10FT±2 inch	MP-54RJ45SNNX-010
15FT±2 inch	MP-54RJ45SNNX-015
25FT±4 inch	MP-54RJ45SNNX-025
50FT±8 inch	MP-54RJ45SNNX-050
100FT±8 inch	MP-54RJ45SNNX-100



PIN OUT: T568B		
PLUG 1	PLUG 2	COLOR
PIN 1	PIN 1	WHITE/ORANGE
PIN 2	PIN 2	ORANGE
PIN 3	PIN 3	WHITE/GREEN
PIN 4	PIN 4	BLUE
PIN 5	PIN 5	WHITE/BLUE
PIN 6	PIN 6	GREEN
PIN 7	PIN 7	WHITE/BROWN
PIN 8	PIN 8	BROWN
Shielded	Shielded	DRAIN WIRE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		DATE		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS		ANGLES		APPROVALS			
X	±X	±X°		DRAWN	LF	25/NOV/2014	
XX	±XX			CHECKED	BA	25/NOV/2014	
XXX	±XXX			RESP ENG			
THIRD ANGLE PROJECTION				SIZE DWG. NO. MP-54RJ45SNNX-XXX			
				SCALE SHEET OF			
DOW FILE:				REV. A5			

Beige:MP-54RJ45SNNX-XXX
Black:MP-54RJ45SNNK-XXX