





REV.	DATE	DESCRIPTION
NC	06/07/99	INITIAL RELEASE
A	03/20/07	UPDATE DRAWING FORMAT, ADD BODY X-SEC.



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
7						DRAWN	G.R.S.	03/20/07								
6						CHECKED										
5						ISSUED				PART DESCRIPTION TNC CRIMP PLUG (RG-178B/U, 196A/U CABLE)						
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		PART NO. 122429							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1												
2	INSULATOR	DELRIN	NATURAL	1					DWG. NO. 122429.DWG							
1	BODY	BRASS	NICKEL	1												
DESCRIPTION MATERIAL FINISH QTY						CAD FILE C:/122/122429.DWG			REV. A		SIZE A		SCALE NA			